

Garant**Indexable insert for turning DNMG 150612, for medium machining****Order data**

Order number	250764 HB7035-2
GTIN	4069515017206
Item class	21G

Technical description

ISO code indexable insert	DNMG 150612
Cutting speed v_c main application	120 - 320 m/min
Number of changes/inserts	4
Type	HB7035-2
Cutting conditions	heavily interrupted
Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Chip breaker	SM
Main application	P
Corner radius	1.2 mm

Data sheet

Tolerance	M
Tool material	Carbide
Type of product	Indexable insert for turning