

**Indexable insert for turning TNMG 160408, for finish machining****Order data**

Order number	251434 HB7020-2
GTIN	4069515017909
Item class	21G

Technical description

Cutting depth a_p	0.3 - 2 mm
ISO code indexable insert	TNMG 160408
Chip breaker	SS
Corner radius	0.8 mm
Type	HB7020-2
Main application	P
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	160 - 400 m/min
Number of changes/inserts	6
Cutting conditions	slightly interrupted
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide

Type of product

Indexable insert for turning