

Garant**GARANT Diabolo solid carbide milling cutter HRC 62 HPC, TiSiN, Ø DC: 2mm****Order data**

Order number	203221 2
GTIN	4069515036566
Item class	11Z

Description**Version:****GARANT Diabolo:**

Special geometry, coating and carbide specially for hard machining.

Specialist for steels up to 62 HRC. Reliable process and longer service life thanks to optimised cutter geometry and state-of-the-art high-performance coating.

Dimensions similar to DIN 6527.

Application:

For peripheral milling as a **finishing operation**.

(plunge cutting only to shallow depths).

Technical description

Corner chamfer angle	90 degrees
Feed f_z for side milling in steel < 60 HRC	0.015 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Cutting edge Ø D_c	2 mm
Flute length L_c	8 mm
Shank Ø D_s	6 mm
No. of teeth Z	4
Overall length L	57 mm
Helix angle	50 degrees

Data sheet

Tolerance nominal Ø	h7
Series	Diabolo
Coating	TiSiN
Tool material	Solid carbide
Standard	DIN 6527
Type	H
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	0.05×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	red
Type of product	Indexable end mill

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable only under restricted conditions	170 m/min	P
Steel < 50 HRC	suitable only under restricted conditions	150 m/min	H
Steel < 55 HRC	suitable	130 m/min	H
Steel < 60 HRC	suitable	100 m/min	H
Steel < 65 HRC	suitable	80 m/min	H
Steel < 67 HRC	suitable only under restricted conditions	65 m/min	H
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/203221-2>

