

Garant**Indexable insert for turning DNMG 110408, for finish machining****Order data**

Order number	250654 HB7010-2
GTIN	4069515016681
Item class	21G

Technical description

Cutting speed v_c main application	170 - 500 m/min
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.8 mm
Type	HB7010-2
Tool material	Carbide
ISO code indexable insert	DNMG110408
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Main application	P
Cutting conditions	continuous

Chip breaker	SS
Type of product	Indexable insert for turning