


**Indexable insert for turning WNMG 080408, for roughing machining****Order data**

Order number	252208 HB7020-2
GTIN	4069515019026
Item class	21G

Technical description

Corner radius	0.8 mm
ISO code indexable insert	WNMG 080408
Main application	P
Number of changes/inserts	6
Tool material	Carbide
Cutting conditions	slightly interrupted
Chip breaker	SG
Cutting depth a_p	1.5 - 6 mm
Feed f	0.25 - 0.6 mm/rev.
Type	HB7020-2
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	110 - 360 m/min

Type of product

Indexable insert for turning