

Garant**Indexable insert for turning VC.T 160404, for finish machining****Order data**

Order number	261372 HB7020-2
GTIN	4069515022477
Item class	21G

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Chip breaker	SS
Main application	P
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	VCMT 160404
Tolerance	M
Corner radius	0.2 mm
Tool material	Carbide
Cutting speed v_c main application	140 - 400 m/min

Data sheet

Type	HB7020-2
Number of changes/inserts	2
Type of product	Indexable insert for turning