

Garant**Indexable insert for turning DC.T 11T302, for finish machining****Order data**

Order number	260356 HB7010-2
GTIN	4069515020268
Item class	21G

Technical description

Tolerance	M
Finishing/roughing assignment	Finishing
Corner radius	0.2 mm
Cutting speed v_c main application	150 - 500 m/min
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Main application	P
Number of changes/inserts	2
Chip breaker	SS
Type	HB7010-2
Tool material	Carbide

Data sheet

Cutting conditions	continuous
ISO code indexable insert	DCMT 11T302
Type of product	Indexable insert for turning