

Garant**Indexable insert for turning VBMT 110304, for finish machining****Order data**

Order number	261144 HB7010-2
GTIN	4069515021852
Item class	21G

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Type	HB7010-2
Feed f	0.07 - 0.25 mm/rev.
Corner radius	0.4 mm
ISO code indexable insert	VBMT 110304
Chip breaker	SS
Main application	P
Number of changes/inserts	2
Cutting speed v_c main application	150 - 500 m/min
Tool material	Carbide
Finishing/roughing assignment	Finishing

Data sheet

Cutting conditions

continuous

Type of product

Indexable insert for turning