

**Wheel brush with shank waved, micro-abrasive, ceramic grit K120, Brush Ø D1× bristle width L1: 70X10mm****Order data**

Order number	574460 70X10
GTIN	4017359672907
Item class	57L

Description**Version:**

Abrasive nylon strands with silicon carbide, crimped into steel sleeve; **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

Wet and dry fine rubbing down of aluminium, steel, stainless steel and plastics. Maximum operating temperature 80 °C.

Technical description

Shank Ø D _s	6 mm
Brush Ø D ₁	70 mm
maximum speed	15000 min ⁻¹
Bristle width L ₁	10 mm
Length of brush section H ₁	20 mm

Data sheet

recommended speed	4000 min ⁻¹
Grinding medium code	Ceramic
Type of product	Wheel brush