


**Indexable insert for turning WNMG 080408, for roughing machining****Order data**

Order number	252208 HB7035-2
GTIN	4069515019040
Item class	21G

Technical description

Main application	P
Corner radius	0.8 mm
Finishing/roughing assignment	Roughing
Cutting depth a_p	1.5 - 6 mm
Cutting conditions	heavily interrupted
Number of changes/inserts	6
Cutting speed v_c main application	100 - 290 m/min
Chip breaker	SG
ISO code indexable insert	WNMG 080408
Tool material	Carbide
Feed f	0.25 - 0.6 mm/rev.
Type	HB7035-2

Type of product

Indexable insert for turning