

**Drill/driver, cordless drill/driver****Order data**

Order number	070215 M12FDDXK2
GTIN	4058546229245
Item class	03L

Description**Version:**

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use. Cordless compact drill / screwdriver with quick-change drill chuck.

- **4-in-1 exchangeable head system with four different attachments.**
- **Only 185 mm overall.**

Supplied with:

Kit with 10-mm metal drill chuck, offset screwdriving attachment, eccentric attachment, 6-mm HEX attachment, including 2 pcs. 12V / 2.0 Ah Li-ion battery M12 B2, charger, HD Box.

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

typical application	Medium
maximum speed 1st speed	0 - 400 min ⁻¹

suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Battery voltage	12 V
Manufacturer's designation	M12 FDDXKIT-202X
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless motor
Suitable for material	Wood
Packaging	Modular case (HD=Heavy Duty)
Type of rechargeable battery	Lithium-ion
Weight	0.9 kg
maximum twist drill size Ø in steel	10 mm
maximum speed 2nd speed	1600 min ⁻¹
Number of rechargeable batteries contained	2
maximum torque hard	34 Nm
Power supply	Mains operated
maximum twist drill size Ø in wood	34 mm
Battery capacity	2 Ah
maximum vibration to EN	<2.5 m/s ²
Type of product	Drill/driver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/070215-M12FDDXK2>