

Garant**Indexable insert for turning DNMG 110408, for finish machining****Order data**

Order number	250654 HB7020-2
GTIN	4069515016704
Item class	21G

Technical description

Tool material	Carbide
Chip breaker	SS
Cutting conditions	slightly interrupted
Type	HB7020-2
Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	160 - 400 m/min
ISO code indexable insert	DNMG110408
Main application	P
Number of changes/inserts	4
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.8 mm

Data sheet

Finishing/roughing assignment

Finishing

Type of product

Indexable insert for turning