



Drill/driver, cordless drill/driver



Order data

Order number	075532 M12FHAC
GTIN	4058546563479
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **SDS plus chuck.**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

12 V / 5.0 Ah FUEL™ cordless combination hammer with brushless POWERSTATE motor.

Optimised for holes from Ø 4 – 10 mm in concrete and masonry. Redlink Plus electronic – overload protection for long working life of the battery, motor and gearbox.

Supplied with:

Zero-speed version – without battery, charger and case. Supplied with quick charger, 2 pcs. 12 V / 5 Ah High-Output battery, HD box.

Note:

Suitable carbide hammer drills can be found from No. 787000.

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

maximum vibration to EN	10.5 m/s ²
Speed range	0 - 1200 min ⁻¹
Number of rechargeable batteries contained	0

Data sheet

Weight	1.9 kg
Type of rechargeable battery	Lithium-ion
Impact energy	1.1 J
maximum twist drill size Ø in steel	10 mm
Quick-clamping chuck range	1.5 - 13 mm
maximum hammer rate	4410 min ⁻¹
maximum twist drill size Ø in wood	13 mm
Manufacturer's designation	M12 FHAC16-0
maximum twist drill size Ø in concrete	13 mm
Battery voltage	12 V
Type of product	Hammer drill