


**Indexable insert for turning WNMG 080408, for medium machining****Order data**

Order number	252070 HB7035-2
GTIN	4069515018906
Item class	21G

Technical description

Corner radius	0.8 mm
Cutting conditions	heavily interrupted
Tolerance	M
Type	HB7035-2
Cutting depth a_p	0.3 - 4 mm
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Tool material	Carbide
Finishing/roughing assignment	Finishing
Chip breaker	SM
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6

Data sheet

Cutting speed v_c main application

120 - 320 m/min

Type of product

Indexable insert for turning