

**Drill/driver, cordless drill/driver****Order data**

Order number	075530 M12FHAC
GTIN	4058546563493
Item class	03L

Description**Version:**

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

12 V / 5.0 Ah FUEL™ cordless combination hammer with brushless POWERSTATE motor.

Optimised for holes from Ø 4 – 10 mm in concrete and masonry. Redlink Plus electronics - overload protection to ensure a long working life for the rechargeable battery, motor and gearbox

Supplied with:

Supplied with rapid charger, 2 pcs. 12V / 5 Ah high-output rechargeable battery, HD-Box.

Note:

Suitable carbide hammer drills can be found from No. 787000.

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

maximum twist drill size Ø in wood	13 mm
Weight	1.9 kg

Data sheet

Impact energy	1.1 J
maximum hammer rate	4410 min ⁻¹
Number of rechargeable batteries contained	2
maximum twist drill size Ø in steel	10 mm
Battery voltage	12 V
Manufacturer's designation	M12 FHAC16-502X
maximum twist drill size Ø in concrete	13 mm
Battery capacity	5 Ah
maximum vibration to EN	10.5 m/s ²
Quick-clamping chuck range	1.5 - 13 mm
Speed range	0 - 1200 min ⁻¹
Type of rechargeable battery	Lithium-ion
Type of product	Hammer drill