

Garant**Indexable insert for turning CNMG 160608, for roughing machining****Order data**

Order number	250334 HB7020-2
GTIN	4069515016360
Item class	21G

Technical description

Number of changes/inserts	4
ISO code indexable insert	CNMG 160608
Main application	P
Feed f	0.25 - 0.6 mm/rev.
Tool material	Carbide
Chip breaker	SG
Cutting speed v_c main application	110 - 360 m/min
Cutting conditions	slightly interrupted
Type	HB7020-2
Corner radius	0.8 mm
Finishing/roughing assignment	Roughing

Data sheet

Cutting depth a_p	1.5 - 6 mm
Type of product	Indexable insert for turning