

Garant**Indexable insert for turning VNMG 160408, for medium machining****Order data**

Order number	251804 HB7010-2
GTIN	4069515018289
Item class	21G

Technical description

Type	HB7010-2
Tolerance	M
Tool material	Carbide
Corner radius	0.8 mm
Main application	P
Number of changes/inserts	4
Cutting depth a_p	0.3 - 4 mm
ISO code indexable insert	VNMG 160408
Cutting conditions	continuous
Chip breaker	SM
Feed f	0.2 - 0.5 mm/rev.

Data sheet

Cutting speed v_c main application	140 - 440 m/min
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning