

Garant**Master Mute boring bar A.. STFCR 90°, for indexable inserts TC., right****Order data**

Order number	265024 40/16
GTIN	4069515037990
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shim	269005 19
Set of insert screws	269028 50
ISO code toolholder	A40X STFCR/L16
Series	Master Mute
Shank $\varnothing D_s$	40 mm
Minimum pre-drill $\varnothing D_{min}$	50 mm
Overhang L_1	240 mm
Overall length L	359 mm
Insert size	16 mm
Setting angle κ	90 degrees
Standard	Works standard
Centre offset L_3	27 mm
Shim screw	269013 8

Data sheet

suitable indexable insert	TC.. 16T3..
L _{min}	240 mm
Application type	right-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265024-40/16>