

Garant**Indexable insert for turning VNMG 160404, for finish machining****Order data**

Order number	251732 HB7010-2
GTIN	4069515018104
Item class	21G

Technical description

ISO code indexable insert	VNMG 160404
Type	HB7010-2
Cutting speed v_c main application	170 - 500 m/min
Chip breaker	SS
Tool material	Carbide
Corner radius	0.4 mm
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.
Main application	P
Finishing/roughing assignment	Finishing
Number of changes/inserts	4

Data sheet

Cutting depth a_p	0.3 - 2 mm
Type of product	Indexable insert for turning