

Garant**SC.T 120408, Grade: HU7310**

Order data

Order number	260766 HU7310
GTIN	4045197670601
Item class	21G

Description

Technical description

Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.8 mm
Main application	N
Cutting conditions	continuous
Chip breaker	AM
Cutting depth a_p	0.1 - 4 mm
Grade	HU7310
Cutting speed v_c main application	350 - 600 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
Coating	uncoated

ISO code indexable insert	SCGT 120408
Number of changes/inserts	4
Tolerance	G
Type of product	Indexable insert for turning