

**Garant****Indexable insert for turning DNMG 110408, for finish machining****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 250654 HB7035-2 |
| GTIN         | 4069515016728   |
| Item class   | 21G             |

**Technical description**

|                                      |                     |
|--------------------------------------|---------------------|
| Number of changes/inserts            | 4                   |
| Feed f                               | 0.1 - 0.4 mm/rev.   |
| Cutting speed $v_c$ main application | 150 - 350 m/min     |
| Corner radius                        | 0.8 mm              |
| ISO code indexable insert            | DNMG110408          |
| Chip breaker                         | SS                  |
| Main application                     | P                   |
| Finishing/roughing assignment        | Finishing           |
| Type                                 | HB7035-2            |
| Cutting conditions                   | heavily interrupted |
| Tool material                        | Carbide             |

## Data sheet

|                     |                              |
|---------------------|------------------------------|
| Cutting depth $a_p$ | 0.3 - 2 mm                   |
| Type of product     | Indexable insert for turning |