


Garant**Indexable insert for turning WNMG 080408, for finish machining****Order data**

Order number	251964 HB7010-2
GTIN	4069515018586
Item class	21G

Technical description

Cutting speed v_c main application	170 - 500 m/min
Main application	P
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	continuous
Cutting depth a_p	0.3 - 2 mm
Chip breaker	SS
Number of changes/inserts	6
ISO code indexable insert	WNMG 080408
Corner radius	0.8 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Type	HB7010-2

Type of product

Indexable insert for turning