

Garant**Indexable insert for turning VBMT 160408, for finish machining****Order data**

Order number	261154 HB7020-2
GTIN	4069515022057
Item class	21G

Technical description

Cutting speed v_c main application	140 - 400 m/min
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Type	HB7020-2
Feed f	0.07 - 0.25 mm/rev.
Main application	P
Chip breaker	SS
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	2
Cutting conditions	slightly interrupted
Tool material	Carbide

Data sheet

ISO code indexable insert

VBMT 160408

Type of product

Indexable insert for turning