

Garant**Indexable insert for turning VC.T 160408, for medium machining****Order data**

Order number	261459 HB7010-2
GTIN	4069515022682
Item class	21G

Technical description

Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting conditions	continuous
Number of changes/inserts	2
Tolerance	M
Main application	P
ISO code indexable insert	VCMT 160408
Type	HB7010-2

Data sheet

Corner radius	0.8 mm
Chip breaker	SM
Type of product	Indexable insert for turning