


**Indexable insert for turning TCMT 110208, for finish machining****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 260954 HB7035-2 |
| GTIN         | 4069515021418   |
| Item class   | 21G             |

**Technical description**

|                                      |                     |
|--------------------------------------|---------------------|
| Chip breaker                         | SS                  |
| Cutting conditions                   | heavily interrupted |
| Type                                 | HB7035-2            |
| Cutting speed $v_c$ main application | 120 - 350 m/min     |
| ISO code indexable insert            | TCMT 110208         |
| Tool material                        | Carbide             |
| Corner radius                        | 0.8 mm              |
| Cutting depth $a_p$                  | 0.2 - 1.5 mm        |
| Main application                     | P                   |
| Number of changes/inserts            | 3                   |
| Feed $f$                             | 0.07 - 0.25 mm/rev. |
| Finishing/roughing assignment        | Finishing           |

Type of product

Indexable insert for turning