



Clamping cam, Threads: M10



Order data

Order number	370052 M10
GTIN	4059245559701
Item class	37K

Description

Advantage:

- **Compact design.**
- **Quick and easy clamping of components.**

Application:

For lateral clamping of narrow and wide workpieces. The workpiece is clamped by tightening the fixture clamp with a spanner.

Material:

Heat treatable steel, burnished

Technical description

maximum tightening torque	75 Nm
Length L	15 mm
Clamping force	8 kN
L ₁	20.5 mm
Height H ₂	15 mm

Data sheet

Height H	20 mm
Ø D	30 mm
AF ₁	8 mm
Width across flats AF	24 mm
Stroke S	5.5 mm
Height H ₁	10 mm
Type of product	Side clamps