



Clamping cam, Threads: M8



Order data

Order number	370052 M8
GTIN	4059245559695
Item class	37K

Description

Advantage:

- **Compact design.**
- **Quick and easy clamping of components.**

Application:

For lateral clamping of narrow and wide workpieces. The workpiece is clamped by tightening the fixture clamp with a spanner.

Material:

Heat treatable steel, burnished

Technical description

Clamping force	5.2 kN
Length L	12 mm
maximum tightening torque	50 Nm
Stroke S	4.4 mm
Height H ₁	8 mm

Data sheet

L ₁	16.4 mm
Height H ₂	12 mm
AF ₁	6 mm
Ø D	24 mm
Height H	16 mm
Width across flats AF	19 mm
Type of product	Side clamps