

Garant**SC.T 09T304, Grade: HU7310**

Order data

Order number	260762 HU7310
GTIN	4045197670366
Item class	21G

Description

Technical description

Main application	N
Chip breaker	AM
Cutting conditions	continuous
Corner radius	0.4 mm
Cutting depth a_p	0.1 - 4 mm
Feed f	0.05 - 0.5 mm/rev.
Grade	HU7310
Cutting speed v_c main application	350 - 600 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
Coating	uncoated

ISO code indexable insert	SCGT 09T304
Number of changes/inserts	4
Tolerance	G
Type of product	Indexable insert for turning