



Centring clamp Form B, Thread × length: M4X12



Order data

Order number	370054 M4X12
GTIN	4059245267781
Item class	37K

Description

Version:

Form B with cylinder head screw.

Advantage:

- **Pull-down effect.**
- **Quick and easy clamping of components.**

Application:

For centring and clamping a workpiece in the hole. High clamping forces are achieved by the wedge surfaces.

Material:

Heat treatable steel, burnished Hardened (33-39 HRC).

Note:

During the clamping process, the clamping force acts on specific points of the hole wall.

Technical description

D _{min}	8 mm
D _{max}	10.3 mm

Data sheet

Width across flats AF	3 mm
L	7.1 mm
maximum clamping force	1.5 kN
H	5.5 mm
H ₁	5.1 mm
Type of product	Jig clamping system