


**Wedge clamp, narrow version smooth, Thread M x length L: M8X25mm****Order data**

Order number	370026 M8X25
GTIN	4059245032693
Item class	37K

Description**Application:**

- **Wedge surfaces produce high clamping forces.**
- **Wedge clamps can be used in tapped holes or T-slots.**
- **When the clamping screw is screwed in, the clamping segments press against the workpieces.**
- **A slot in the double wedge allows for movement and tolerance adjustment. Movement distance: M8 = ± 0.5 mm; M10 and M12 = ± 1.0 mm; M16 = ± 1.5 mm.**
- **Wedge clamps are suitable for multiple clamping.**

Material:

Double wedge and clamping segments heat-treatable steel, hardened, black.

Technical description

Thread	M8
Length L	25 mm
Width B	24 mm
Height E	2 mm

Data sheet

Height C	15 mm
A maximum	33.5 mm
A minimum	30.5 mm
maximum clamping force	15 kN
Type of product	Side clamps