




Wedge clamp, narrow version serrated, Thread M x length L: M8X25mm



Order data

Order number	370027 M8X25
GTIN	4059245032778
Item class	37K

Description

Application:

- **Wedge surfaces produce high clamping forces.**
- **Wedge clamps can be used in tapped holes or T-slots.**
- **When the clamping screw is screwed in, the clamping segments press against the workpieces.**
- **A slot in the double wedge allows for movement and tolerance adjustment. Movement distance: M8 = ± 0.5 mm; M10 and M12 = ± 1.0 mm; M16 = ± 1.5 mm.**
- **Wedge clamps are suitable for multiple clamping.**

Material:

Double wedge and clamping segments heat-treatable steel, hardened, black.

Technical description

Length L	25 mm
Thread	M8
Height E	2 mm
Width B	24 mm

Data sheet

Height C	15 mm
A maximum	33.5 mm
A minimum	30.5 mm
maximum clamping force	15 kN
Type of product	Side clamps