

Garant**GARANT Master Uni cutting disc EXTRA THIN, steel, INOX, Disc Ø: 115mm****Order data**

Order number	563240 115
GTIN	4069515040242
Item class	51M

Description**Version:**

Self-sharpening **ceramic grit (CER)** and the newly developed **high-performance bonding system** permit **grinding performance that is many times better, long-lasting aggressive performance and extremely cool grinding** compared to conventional cutting discs (A).

- **Very high productivity thanks to very quick separating cuts.**
- **Optimum balance between extremely soft cutting behaviour with very low application force and very long service life.**
- **Specification: CER60Q-BF.**

Technical description

Disc Ø	115 mm
Bore Ø	22.23 mm
Shape description	flat
Disc thickness	1 mm
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Uni	suitable only under restricted conditions		
dry	suitable		