

Rough grinding wheel PREMIUM*** Focur, Disc Øxdisc width: 125X7mm



Order data

Order number	560150 125X7
GTIN	9003173158937
Item class	53T

Description

Version:

Special type for grinding cast iron. High-quality zirconium aluminium oxide and silicon carbide permit very high metal removal rates at low contact forces, even on castings with burnt-on residues. Specification: ZA24P-BFP. Grit, bonding, abrasive additives as well as reinforcement of the rough grinding discs are optimised for maximum metal removal rate and working life in their respective applications. Shapes: Rough grinding discs, depressed centres (shapes 27, 28, 29) Grinding angle 20° to 30° Application: On electric and pneumatic angle grinders with maximum 80 m/s circumferential speed for grinding welds, surfaces, and edges.

Technical description

Disc thickness	7 mm
Disc Ø	125 mm
Bore Ø	22.23 mm
Grinding medium code	ZA
Specification	A24Q-BFX
recommended approach angle	20-30 degrees

optimised for material	Cast iron
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

User data

	Suitability	V_c	ISO code
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
GG(G)	suitable		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		