

## Garant

### Toolholder cranked – external 90°, left-hand, Shank width b: 25mm



#### Order data

Order number	273806 25
GTIN	4045197500014
Item class	21W

#### Description

##### Version:

- **Extremely still connection and precise clamping due to serrated contact face between the tool holder and clamp.**
- **To ensure the optimum connection, the maximum tightening torque for the attachment screw is laser-etched on the shank.**
- **Very high positioning accuracy, together with very high resistance to axial and radial cutting forces.**

##### Suitable for :

Blade carriers No. 273820; 273822; 273824; 273828.

##### Supplied with:

Including assembly screws.

##### Note:

Tool holders must be ordered separately.

Head length  $L_1$ : 20.5 mm

Overall length L: 160 mm

$L_2$ : 38 mm

Screw: 279815 9 (TX25; 6 Nm)

#### Technical description

Head length $L_1$	20.5 mm
Shank width b	25 mm
$L_2$	38 mm
Screw	279815 9 (TX25; 6 Nm)

Overall length L	160 mm
Application type	left-hand
Type of product	Clamping toolholder

---

## Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX25	674248 TX25
Clamping screw Type 9	279815 9
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Clamping screw	279910
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50