



Combination face mill adapter, SK 50 A = 55, Spigot Ø d1: 40mm



Order data

Order number	302520 40
GTIN	4250122600855
Item class	36E

Description

Version:

Internal thread for manual clamping.

Application:

With drive key for milling cutters **with longitudinal groove**, e.g. DIN 841.

With face mill drive ring for milling cutters with **transverse slots**, DIN 1880.

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Special toggle spanner No. 309840.

Technical description

Milling mandrel length L ₄	41 mm
Overhang dimension A	55 mm
Spare drive ring No. 309870	40
Milling mandrel length L ₃ with drive ring	27 mm
Overall length L	209 mm
Spigot Ø d ₁	40 mm
Suitable toggle spanner No. 309840	40
Thread M	M24
Spare milling cutter lock screw No. 309860 / 309861	40

Clamping Ø D ₁	40 mm
Adapter	SK 50 A = 55
Standard	DIN 6358
Arbor standard	DIN 2080
Concentricity	≤ 6 µm
Type of product	Milling cutter spigot

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/302520-40>