

**Garant****Shrink-fit chuck, SK 40 A = 130, Clamping range  $\varnothing$  D1: 16mm****Order data**

Order number	302266 16
GTIN	4045197646132
Item class	31A

**Description****Version:**

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

**Application:**

For clamping tools with parallel shank to h6 tolerance.  
Suitable for inductive, contact, and hot-air shrink units.

**Optional extras:**

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	16 mm
Overhang dimension A	130 mm
$\varnothing$ D <sub>2</sub>	27 mm
External $\varnothing$ D	34 mm
Adapter	SK 40 A = 130
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Pull studsealed suitable for steep tapers 40	308635 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/16 mm	302410 32/16
Pull studsealed, form B suitable for steep tapers 40	308650 40
Shrink-fit unit Type SU1	354210 SU1
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/16 mm	302416 25/16
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Cooling adapter long4.5° for clamping Ø 12,1-16 mm	354236 12,1-16
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/16 mm	302410 25/16
Screening plate for coilSU1 for clamping Ø 12-20 mm	354240 12-20
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 32/16 mm	302412 32/16
	302416 32/16

Shrink-fit chuck extension 4.5° without length adjustment  
screw  $\varnothing d / \varnothing D1$  32/16 mm

Pull studsealed suitable for steep tapers 40	308660 40
--	-----------

Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
---	-----------

Basic tool mountingfor SK for SK taper shank 40	354225 40
---	-----------

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
---	-----------

Special pull stud with internal thread suitable for steep tapers 40	308740 40
---	-----------

Shrink-fit chuck extension 4.5° with length adjustment screw $\varnothing d / \varnothing D1$ 25/16 mm	302412 25/16
---	--------------

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
--	-----------

Pull stud 45°sealed suitable for steep tapers 40	308765 40
--	-----------

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
--	-----------

Cooling adapter short4.5° for clamping $\varnothing 12,1-16$ mm	354235 12,1-16
---	----------------

Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
--	-----------

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
--	-----------

Pull stud 90°sealed suitable for steep tapers 40	308795 40
--	-----------

Pull studsealed, form A suitable for steep tapers 40	308610 40
--	-----------

Pull stud 90°sealed suitable for steep tapers 40	308790 40
--	-----------

Cooling unit Type CU1	354215 CU1
-----------------------	------------

Pull stud 45°sealed suitable for steep tapers 40	308760 40
--	-----------

Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
---	-----------

Pull studForm B suitable for steep tapers 40	308640 40
--	-----------

Pull studMazak, form A suitable for steep tapers 40M	308670 40M
--	------------