

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 10/11 mm**

**Order data**

Order number	260918 10/11
GTIN	4045197653369
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	12 mm
Pack of insert screws	269028 7
ISO code toolholder	E10K STF CR/L11
suitable indexable insert	TC.. 1102..
Centre offset $L_3$	6 mm
Head length $L_1$	16 mm
Insert size	11 mm
Overall length $L$	125 mm
Clamping height $L_2$	9.6 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500