

**Garant****ER clamping nut High Speed, for ER: 25****Order data**

|              |               |
|--------------|---------------|
| Order number | 309595 25     |
| GTIN         | 4069515040655 |
| Item class   | 31Z           |

**Description****Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With slots.**

**Suitable for:**

All standard ER collet chucks.

**Optional extras:**

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

**Note:**

Collet chuck and clamping nut are balanced separately!

**Technical description**

|                           |         |
|---------------------------|---------|
| External Ø D              | 42 mm   |
| maximum tightening torque | 140 Nm  |
| Thread                    | M32x1.5 |

## Data sheet

|                  |              |
|------------------|--------------|
| Overall length L | 21 mm        |
| Standard         | DIN 6499 D   |
| Type of product  | Clamping nut |