

Garant**Cargo scooter, Type: CS****Order data**

Order number	915650 CS
GTIN	4069515040761
Item class	9GZ

Description**Version:**

Stable scooter for fast and safe internal transport of tools and materials. Cannot tip over due to 3 wheels, Ø 200 mm, with treadless TPU tyres, minimum rolling resistance, low noise and fibre shields. Footplate with non-slip surface for a secure foot position. With foot brake and bell, handlebar fixing using padlock. Handles with 2-component Haptoprene for maximum comfort – even with wet or oily hands. Practical loading platform with bamboo board and removable safety bar. With perforated panel on both sides □ 9 x 9 mm in a 37 mm grid, to hold GARANT easyFix hooks and holders, as well as perforated panel accessories. With a drawer under the loading platform.

Optional extras:

Drawer attachment No. 915660; L-BOXX® holder No. 915663; padlock No. 085880 size 30.

Colour:

RAL 7016 anthracite, powder coated.

Note:

Cargo scooter for internal transport only. Must not be used in road traffic. **Use only on flat industrial floors.**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Data sheet

Weight	47 kg
Width	700 mm
Load capacity of loading area	50 kg
Height	988 mm
Wheel Ø	200 mm
Length	1510 mm
Brake	yes
Safe working load	200 kg
Load face length	592 mm
Platform area width	697 mm
Material of storage shelf	Bamboo
Material of wheel	treadless TPU tyres
Hoffmann perforated panel grid interval	9×9
Type of product	Cargo scooter with loading platform