

Garant
Shrink-fit chuck slim, SK 50 A = 120, Clamping range \varnothing D1: 6mm

Order data

Order number	302342 6
GTIN	4045197505347
Item class	31A

Description
Version:

- All shanks hard turned (for smooth running!).
- With RFID / Balluffchip bore.
- Integral tool length adjustment, range 10 mm available only from size 6 upwards!
- Extra slim design(reduced interference contour).

Application:

- Cutting operations in tool and mould making.
- For clamping tools with parallel shank to h6 tolerance.

Optional extras:

Pull studs (PS) No. 308600 – 308806. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fitting units No. 354210 – 354450.

Technical description

\varnothing D ₂	15 mm
Clamping \varnothing D ₁	6 mm
Overhang dimension A	120 mm
External \varnothing D	30.9 mm
Adapter	SK 50 A = 120
Arbor standard	ISO 7388-1
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Shrink-fit unit Type SU1	354210 SU1
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 20/6 mm	302416 20/6
Pull stud sealed suitable for steep tapers 50	308660 50
Pull stud Form B suitable for steep tapers 50	308640 50
Cooling adapter long 4.5° for clamping Ø 6-9 mm	354236 6-9
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/6 mm	302415 20/6
Screening plate for coil SU1 for clamping Ø 6-12 mm	354240 6-12
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Shrink-fit chuck extension 4.5° without length adjustment screw, with through coolant holes Ø d / Ø D1 20/6 mm	302414 20/6
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 16/6 mm	302412 16/6
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud sealed, form A suitable for steep tapers 50	308610 50
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 20/6 mm	302410 20/6
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 20/6 mm	302412 20/6

Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Basic tool mountingfor SK for SK taper shank 50	354225 50
Cooling adapter short4.5° for clamping Ø 6-9 mm	354235 6-9
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 16/6 mm	302410 16/6
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Cooling unit Type CU1	354215 CU1
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull studsealed, form B suitable for steep tapers 50	308650 50