



Hydraulic chuck extension, L = 150 mm, Shank \varnothing d / Clamping range \varnothing D1: 20/12mm



Order data

Order number	302375 20/12
GTIN	2050001740946
Item class	33W

Description

Version:

With axial length adjustment. Flexible due to use of reducing sleeves.

Application:

Suitable for hydraulic chucks and collet chucks.

Optional extras:

Reducing sleeves No. 302135 – 302187.

Technical description

Overhang dimension A	100 mm
Shank \varnothing d	20 mm
L_1	46 mm
Adjustment travel V	10 mm
Thread M	M10x1
Clamping \varnothing D ₁	12 mm
External \varnothing D	25 mm
Overall length L	150 mm
Product name attribute	L = 150 mm
Type of product	Hydraulic clamping chuck accessories

Accessories

Slotted reducing adaptersealed Clamping range Ø D1 6 mm	302140 6
Slotted reducing adaptersealed Clamping range Ø D1 3 mm	302140 3
Slotted reducing adaptersealed Clamping range Ø D1 4 mm	302140 4
Slotted reducing adapterwith cooling Clamping range Ø D1 3 mm	302135 3
Slotted reducing adapterwith cooling Clamping range Ø D1 6 mm	302135 6
Slotted reducing adapterwith cooling Clamping range Ø D1 8 mm	302135 8
Slotted reducing adapterwith cooling Clamping range Ø D1 4 mm	302135 4
Slotted reducing adaptersealed Clamping range Ø D1 8 mm	302140 8
Slotted reducing adaptersealed Clamping range Ø D1 5 mm	302140 5
Slotted reducing adapterwith cooling Clamping range Ø D1 5 mm	302135 5