



Drill/driver, cordless drill/driver



Order data

Order number	070215 M12FDD2-4
GTIN	4058546376680
Item class	03L

Description

Version:

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Brushless POWERSTATE™ motor for more power and a compact shape (168 mm in length).**
- **REDLINK PLUS™ electronics for intelligent power management and overload protection.**
- **16-Step electronic torque limit setting, plus drill steps.**

Advantage:

REDLINK PLUS™ electronics.

Supplied with:

Supplied with 2 pcs. 12 V / 4.0 Ah Li-ion batteries, charger, belt clip, HD box.

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

Motor design	Brushless motor
maximum vibration to EN	<2.5 m/s ²
maximum twist drill size Ø in wood	35 mm
maximum speed 1st speed	0 - 450 min ⁻¹
Packaging	Modular case (HD=Heavy Duty)
Battery voltage	12 V
Suitable for material	Steel
Suitable for material	wood
Suitable for material	Metal
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Manufacturer's designation	M12FDD-402X
maximum torque hard	44 Nm
Weight	1.4 kg
Battery capacity	4 Ah
Quick-clamping chuck range	1.5 - 13 mm
Power supply	Mains operated
maximum twist drill size Ø in steel	13 mm
maximum speed 2nd speed	1700 min ⁻¹
typical application	Strong
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Type of product	Drill/driver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/070215-M12FDD2-4>