

Garant**Master Mute boring bar A.. SCLCR 95°, for indexable inserts CC., right****Order data**

Order number	265008 20/09
GTIN	4069515024464
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{\min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Setting angle κ	95 degrees
Centre offset L_3	13 mm
ISO code toolholder	A20X SCLCR/L09
Overhang L_1	120 mm
Series	Master Mute
Overall length L	189 mm
Shank $\varnothing D_s$	20 mm
Insert size	9 mm
Standard	Works standard
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	CC.. 09T3..
Set of insert screws	269028 50
L_{\min}	120 mm

Application type	right-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265008-20/09>