

**Internal turning tool right-hand similar to DIN 4953, HSS E, Shank Ø: 10mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 296300 10     |
| GTIN         | 4045197189042 |
| Item class   | 22E           |

**Description****Version:**

All dimensions **welded**.

**Application:**

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

**Technical description**

|                  |              |
|------------------|--------------|
| for bores from Ø | 20 mm        |
| Shank Ø          | 10 mm        |
| Overall length   | 160 mm       |
| Tool material    | HSS E        |
| Type of product  | Turning tool |