

Garant**Master Mute boring bar A.. SCLCL 95°, for indexable inserts CC., left****Order data**

Order number	265009 20/09
GTIN	4069515024556
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Overall length L	189 mm
Setting angle κ	95 degrees
Set of insert screws	269028 50
Centre offset L_3	13 mm
Shank $\varnothing D_s$	20 mm
Overhang L_1	120 mm
ISO code toolholder	A20X SCLCR/L09
Standard	Works standard
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Series	Master Mute
Minimum pre-drill $\varnothing D_{min}$	25 mm
L_{min}	120 mm

Data sheet

Connection thread	G1/4
Application type	left-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265009-20/09>