



Master Mute boring bar A.. SDUCR 93°, for indexable inserts DC., right



Order data

Order number	265014 08/07
GTIN	4069515024594
Item class	29E

Description

Version:

Round shank without clamping face. Carbide-reinforced shank.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank $\varnothing D_s$	8 mm
Overall length L	128 mm
Set of insert screws	269028 38
Centre offset L_3	8 mm
suitable indexable insert	DC.. 0702..
Insert size	7 mm
Overhang L_1	88 mm
ISO code toolholder	A08X SDUCR/L07
Minimum pre-drill $\varnothing D_{min}$	13 mm
Series	Master Mute
Setting angle κ	93 degrees
Standard	Works standard
Connection thread	M7×0.5

Data sheet

Application type	right-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar