

Garant**Master Mute boring bar A.. SDUCL 93°, for indexable inserts DC.., left****Order data**

Order number	265015 20/11
GTIN	4069515024761
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank $\varnothing D_s$	20 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
Overall length L	189 mm
Overhang L_1	120 mm
Setting angle κ	93 degrees
Set of insert screws	269028 50
Standard	Works standard
Insert size	11 mm
Centre offset L_3	13 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A20X SDUCR/L11
Series	Master Mute
L_{min}	120 mm

Data sheet

Connection thread	G1/4
Application type	left-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar