

**Torque screwdriver, fixed setting, without scale, set torque: 2,5N·m****Order data**

|              |               |
|--------------|---------------|
| Order number | 659890 2,5    |
| GTIN         | 4069515041799 |
| Item class   | 62E           |

**Description****Version:**

Torque screwdriver with easy-grip 2-component handle and **fixed torque**. When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. Suitable for clockwise tightening. **It is not possible to tighten the screw any further.**

**Advantage:**

Torque screwdriver can be used with all conventional bits C 6.3 and E 6.3 (similar to No. 675155, 675390).

**Application:**

For controlled tightening of screws to a pre-set torque.  
Ideal for fitting indexable inserts.

**Standard:**

Tested to **DIN EN ISO 6789**.

**Accuracy:**

±10% of the specified value.

**Note:**

All Wiha interchangeable blades (No. 659940 – 659946) can also be used in the HOLEX torque screwdriver No. 659945.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

The set torque value **cannot** be changed.

**Technical description**

|                    |          |
|--------------------|----------|
| Release signalling | acoustic |
| Release signalling | haptic   |

## Data sheet

|                           |                        |
|---------------------------|------------------------|
| Torque measuring accuracy | ±10 %                  |
| Measurement process       | Torque                 |
| Calibration               | O1                     |
| Measurement technology    | mechanical             |
| Standard                  | DIN EN ISO 6789        |
| Trigger principle         | mechanical slip clutch |
| Overall length L          | 168 mm                 |
| Adjustable trigger value  | non-adjustable         |
| Display                   | analogue               |
| Data can be recorded      | no                     |
| Feedback                  | acoustic signal        |
| Feedback                  | triggering             |
| Connection format         | Bit holder 1/4 inch    |
| Bit socket                | D 6.3                  |
| Bit socket                | F 6.3                  |
| Setting the trigger value | preset                 |
| Direction of tightening   | Right-hand tightening  |
| set torque                | 250 cNm                |
| set torque                | 2.5 Nm                 |
| Torque fixed setting      | yes                    |
| Type of product           | Torque screwdriver     |

### Suitable products

No Shop URL available for: 659890 2,5