



## Hook turning tool right-hand similar to DIN 4963, HSS E, Shank Ø: 16mm



### Order data

Order number	297120 16
GTIN	4045197190666
Item class	22E

### Description

#### Version:

All dimensions **welded**.

#### Application:

Universally applicable, medium cutting speeds.

**HSS/E** – On all lathes in one-off and volume production. These turning tools have a high cutting performance and carry a low risk of fracture, even at large cutting depths, interrupted machining, or when cutting high strength materials.

### Technical description

Blade width	4 mm
maximum grooving depth $t_{max}$	10 mm
for bores from Ø	32 mm
Shank Ø	16 mm
Overall length	210 mm
Tool material	HSS E
Type of product	Turning tool