

Garant**Master Mute boring bar A.. STFCR 90°, for indexable inserts TC.., right****Order data**

Order number	265024 20/11
GTIN	4069515024846
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Standard	Works standard
suitable indexable insert	TC.. 1102..
ISO code toolholder	A20X STFCR/L11
Minimum pre-drill $\varnothing D_{min}$	25 mm
Set of insert screws	269028 47
Series	Master Mute
Centre offset L_3	13 mm
Overhang L_1	120 mm
Overall length L	189 mm
Insert size	11 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	20 mm
L_{min}	120 mm

Application type	right-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265024-20/11>